

Specifications

Type	UPP-1 positive plate	UPP-2 positive PS plate (high sensitivity)
Spectral sensitivity	320-450nm	
Exposure time	30 seconds; about 20 pulses	20 seconds; about 14 pulses
	(3000w Iodine-Gallium lamp, from 1m, UGRA PCW82 control strip, the third section un-inking)	
Developing time	20-40 seconds (developer : water= 1: 7, $23 \pm 2^{\circ}\text{C}$)	
Resolution	200lpi (2-98%)	
Run-length	varies with its printing conditions and imaging content	
Safelight	yellow light, or fluorescent lamp with UV filter film	