


Product structure diagram



Detail parameter

Driving type	Plug and play without driver		USB line length	≥140cm
Output format	Resolving power			
MJPG	2560*1440P	1920*1080P	1440*1080P	1280*720P
H.264	2560*1440P	1920*1080P	1440*1080P	
YUY2	1280*720P	1024*576P	800*600P	
Sensor type	CMOS	Interface type	USB 2.0	
Scintillation control	50Hz/60Hz	Microphone	Built-in microphone	
Focusing range	Either near or far		Product size	76*48*56.5mm
Support device	Win7, Win8, Win10 and other mainstream windows operating systems, as well as Mac OS, Vista, Linux operating systems			

Installation steps



1.Open the multi-functional base,Point the camera to the front of the display.




2.Press down on the emulti-functional base, fasten it at the front,and keep the back close to the bake of the display,



3.Plug the USB data cable into the USB interface of the computer.


How to use fill light



1. After installing the camera, tap the top of the camera (as shown in the picture) to search for the touch position of the fill light shown to turn on the fill light.
2. Tap again to switch the brightness of the light. There are three levels to switch.
3. Tap the fourth time to turn off the fill light.

Product accessories

Webcam*1



Instructions*1



尺寸：98*55mm